



Guided microwave level transmitter

- Universal level transmitter for liquids and bulk materials
- 4...20 mA/Hart 2 wires
- Insensitive to dust and steam
- ATEX approvals ⟨€x⟩

Type 8185 can be combined with...





Type 8611 Universal PI controller eControl

Type 8635

SideControl EEx

The Type 8185 is a level transmitter with cable or rod probe, designed for continuous level measurement. The unit is suitable for liquids, but also for solids, for industrial use in all areas of process technology.

With measuring range of up to 32 m, the transmitter is best suited for tall vessels.

Even process conditions such as strong steam generation, density fluctuations or changes of the dielectric constant do not influence the accuracy of the measurement.

Buildup or condensation on the probe or vessel wall do not influence the measuring result.







PLC

Type 2712 (8630)

Continuous TopControl system

Process temperature

Process pressure

Temperature drift Accuracy

Type 8644Valve islands

General data	
Materials	
Housing / Cover	PBT, Stainless steel 316L / PC
Seal ring / Ground terminal	NBR / Stainless steel 316L
Wetted parts	
Process fitting / process seal	Stainless steel 316L (1.4435) and PCTFE / FKM
Inner conductor	
(up to the separation cable/rod)	Stainless steel 1.4462
Rod-ø 6 mm	Stainless steel 316L (1.4435)
Cable-ø 4 mm with gravity weight	Stainless steel 316 (1.4401)
Display	LCD in full dot matrix
Weight	
Housing	890 g
Rod-ø 6 mm	approx. 220 g/m
Cable-ø 4 mm	approx. 80 g/m
Gravity weight (only with cable version)	approx. 325 g
Process fitting	Thread G or NPT - 3/4", 1"
Length	
Rod-ø 6 mm	0.3 4 m - Lateral load: 4 Nm
Cable-ø 4 mm	1 32 m - Max. tensile load: 5 KN
Electrical connections	Cable gland M20 x 1.5
Measuring type	Level of liquids and solids
Min. dielectric figure	εr > 1.6
Dead zone	
Rod-ø 6 mm	From top of probe: 80 mm - from bottom of probe: 0 mm
Cable-ø 4 mm	From top of probe: 150 mm - from bottom of probe: 250 mm
Measuring range	0.08 4 m or 0.15 32 m (see diagram on next page)

-30 up to 150°C


0.06%/10K (Relating to the max. measuring range)

See accuracy diagram, on next page


-1 up to 40 bar (-100...4000 kPa) (depends on the process fitting)

burkert


Electrical data				
Power supply	14 to 36 V DC or 14 to 30 V DC (EEx ia instrument)			
Lightening power consumption	approx. 80 mW			
Permissible residual ripple	< 100 Hz: U _{ss} <1 V			
	100 Hz10 kHz: U _{ss} <10 m V			
Output signal	420 mA/HART			
Resolution	1.6 μΑ			
Fault signal	current output unchanged; 20.5 mA; 22 mA < 3.6 mA (adjustable)			
Current limitation	22 mA			
Load	see load diagram			
Integration time (63% of the input variable)	0999 s, adjustable			
Fulfilled NAMUR recommendation	NE 43			
Environment				
Ambient temperature				
with display, adjustment elements	-20 up to +70°C (operation and storage)			
Relative humidity	45-75 %; non condensated			
Standards and approvals				
Protection	IP66/IP67 with M20 x 1.5 gland mounted and tightened			
Overvoltage category	III			
Protection class	II			
Standard				
EMC	EN61326			
Security	EN61010-1			
ATEX	EN50014; EN50020; EN50284			
NAMUR	NE 21; NE 43			
Specifications EEx				
⊕ - Protection	Categories 1/2 G or 2G			
- Certification	EEx ia IIC T6			
Conformity specifications ¹⁾				
Power supply Ui	30 V			
Short circuit rating li	131 mA			
Power limitation Pi	983 mW			
Ambient temperature	-20 up to +41°C (depend on categories)			
Internal capacity Ci	negligible			
Internal inductivity Li	negligible			



1) homologation certificate PTB 07 ATEX 2007 X







Principle of operation

High frequency microwave pulses are guided along a steel cable or a rod. When they reach the product surface, the microwave pulses are reflected and received by the processing electronics. The running time is valuated by the instrument and outputted as distance.

Time consuming adjustement with medium is not necessary. The instruments are preset to the ordered probe length.

The shortenable cable and rod versions can be adapted individually to the local requirements.

Target applications with Type 8185

Foodstuffs and animal feed


Products such as beer, milk, wine, cereals, sugar, flour, coffee, cornflakes, cacao, instant powder, animal feed - liquids or bulk solids levels must be measured everywhere in the food industry.

The microwave principle works independent of products characteristics such as moisture, intense dust or noise generation, density, temperature, overpressure, foal, dielectric value and the shape of the material cone.

Chemical industrie


Many finished products in the chemical industry are produced as powder, granules, pellets, solvents.... The different and sometimes fluctuating product characteristics place heavy demands on the level measurement.

The measuring result is influenced neither by fluctuating product quality nor by dust generation, density, temperature, overpressure, foam or buildup.



burkert

Dimensions [mm]





Ordering chart for compact transmitter Type 8185

Specifications	Voltage supply	Output	Probe	Length	Electrical	Item no. with program module and display	Item no. without program module no display
G 3/4" mounting thread	14-36 V DC	4-20 mA/HART	Rod	1 m	Cable gland M 20 x 1.5	558 229	559 247
		(2 wires)		2 m	Cable gland M 20 x 1.5	558 233	559 251
			Cable	5 m	Cable gland M 20 x 1.5	558 241	559 259
				10 m	Cable gland M 20 x 1.5	558 245	559 263
G 1" mounting thread 1	14-36 V DC	4-20 mA/HART	Rod	1 m	Cable gland M 20 x 1.5	558 231	559 249
		(2 wires)		2 m	Cable gland M 20 x 1.5	558 235	559 253
			Cable	5 m	Cable gland M 20 x 1.5	558 243	559 261
				10 m	Cable gland M 20 x 1.5	558 247	559 265
NPT 3/4" mounting thread 14-	14-36 V DC	4-20 mA/HART (2 wires)	Rod	1 m	Cable gland M 20 x 1.5	558 230	559 248
				2 m	Cable gland M 20 x 1.5	558 234	559 252
			Cable	5 m	Cable gland M 20 x 1.5	558 242	559 260
				10 m	Cable gland M 20 x 1.5	558 246	559 264
NPT 1" mounting thread	14-36 V DC	4-20 mA/HART (2 wires)	Rod	1 m	Cable gland M 20 x 1.5	558 232	559 250
				2 m	Cable gland M 20 x 1.5	558 236	559 254
			Cable	5 m	Cable gland M 20 x 1.5	558 244	559 262
				10 m	Cable gland M 20 x 1.5	558 248	559 266
EEx version - ATEX approval	14-30 V DC	4-20 mA/HART (2 wires)	Rod	1 m	Cable gland M 20 x 1.5	558 237	559 255
G 3/4" mounting thread				2 m	Cable gland M 20 x 1.5	558 239	559 257
			Cable	5 m	Cable gland M 20 x 1.5	558 249	559 267
				10 m	Cable gland M 20 x 1.5	558 251	559 269
EEx version - ATEX approval	14-30 V DC	4-20 mA/HART	Rod	1 m	Cable gland M 20 x 1.5	558 238	559 256
G 1" mounting thread		(2 wires)		2 m	Cable gland M 20 x 1.5	558 240	559 258
			Cable	5 m	Cable gland M 20 x 1.5	558 250	559 268
				10 m	Cable gland M 20 x 1.5	558 252	559 270

Further versions on request

Port connection Thread G or NPT 1"1/2 Flange DN25, DN40, DN50, DN80, DN100, DN150 Flange 1", 1"1/2, 2", 3", 4", 6"

Ordering chart - accessories for transmitter Type 8185 (has to be ordered separately)

Specifica- tions	Item no.
Set with 2 reductions M 20 x 1.5 / NPT1/2" + 2 neoprene flat seals for cable gland + 2 screw-plugs M 20 x 1.5	551 782
Spare cable with gravity weight - 5 m	xxx xxx
Spare cable with gravity weight - 10 m	560 769
Spare rod - 1 m	xxx xxx
Spare rod - 2 m	xxx xxx
Clamp collar	559 765
Program module with display	559 279



Guided microwave level transmitter Type 8185 - request for quotation Please fill in and send to your local Bürkert Sales Centre* with your inquiry or order.						
Company:			Contact person:		in the PD before pr out the fo	
Customer No.:			Department:		out and	
Address:			Tel. / Fax.:			
Postcode / Town:			E-mail:			
Guided microwave lo	evel transmitter 8185					
	Quantity:		Desired delivery date:			
Process fitting con	nection:					
External thread	G 3/4"	☐ G 1"	G 1"1/2			
	■ NPT 3/4"	NPT 1"	■ NPT 1"1/2			
Flange	☐ DN 25	□ DN 40	☐ DN 50			
	☐ DN 80	☐ DN 100	☐ DN 150			
	ANSI 1"	ANSI 1"1/2	ANSI 2"			
	ANSI 3"	ANSI 4"	ANSI 6"			
Sensor version:						
Probe	Rod	Cable				
Length	☐ 1 m	☐ 2 m	□ 5 m	☐ 10 m		
	Spec. length	mm (multiple of (multiple of				
Program module a	nd display	Yes	☐ No			
ATEX approval		Yes	□No			

Type 2712 with 8630 Valve with TopControl system Type 2100 Angle seat valve

*To find your nearest Bürkert facility, click on the orange box \rightarrow

www.burkert.com

In case of special application conditions, please consult for advice.

Subject to alteration.
© Christian Bürkert GmbH & Co. KG

0810/6_EU-en_00895008